



MSR Gold™ MiniFastFit (Touring/Stage)

MSR Gold™ 1000 MiniFastFit 1CT/4

Thanks to the specially designed lamp base, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

Product data

General Information						
Cap-Base	PGJX36 [PGJX36]					
Operating Position	UNIVERSAL [Any or Universal (U)]					
Main Application	Entertainment					
Life to 50% Failures (Nom)	900 h					
System Description	MiniFastFit					
Light Technical						
Color Code	- [Not Specified]					
Luminous Flux (Min)	74000 lm					
Luminous Flux (Nom)	82000 lm					
Chromaticity Coordinate X (Nom)	0.321					
Chromaticity Coordinate Y (Nom)	0.330					
Correlated Color Temperature (Nom)	6000 K					
Luminous Efficacy (Rated) (Nom)	82 lm/W					
Color Rendering Index (Nom)	80					
Operating and Electrical						
Power (Rated) (Nom)	1000.0 W					

Lamp Current (Nom)	11.4 A					
Ignition Supply Voltage (Min)	198 V					
Controls and Dimming						
Dimmable	Yes					
Mechanical and Housing						
Cap-Base Information	PGJX36					
Luminaire Design Requirements						
Bulb Temperature (Max)	950 °C					
Pinch Temperature (Max)	500 °C					
Product Data						
Full product code	871829178508800					
Order product name	MSR Gold™ 1000 MiniFastFit 1CT/4					
EAN/UPC - Product	8718291785088					
Order code	928171405115					
Numerator - Quantity Per Pack	1					

Datasheet, 2018, June 26 data subject to change


MSR Gold™ MiniFastFit (Touring/Stage)

Numerator - Packs per outer box	4
Material Nr. (12NC)	928171405115
Net Weight (Piece)	0.055 kg

Warnings and Safety

• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Dimensional drawing



MSR GOLD 1000 MiniFastFit

Product	D (max)	0	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR Gold™	26 mm	5.5	55 mm	57 mm	56	112 mm	36.5	36	35.3
1000		mm			mm		mm	mm	mm
MiniFastFit									
1CT/4									

